



MSR Gold™ FastFit

MSR Gold™ 2000/1 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

Product data

General Information	
Cap-Base	PGJX50 [PGJX50]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Entertainment
Life to 50% Failures (Nom)	750 h
Light Technical	
Luminous Flux (Min)	155000 lm
Luminous Flux (Nom)	172000 lm
Chromaticity Coordinate X (Nom)	329
Chromaticity Coordinate Y (Nom)	333
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color Rendering Index (Nom)	90
Operating and Electrical	
Power (Rated) (Nom)	2000 W

Lamp Current (Nom)	18.2 A
Ignition Supply Voltage (Max)	198 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	PGJX50
Luminaire Design Requirements	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	500 °C
Product Data	
Full product code	871869667944900
Order product name	MSR Gold™ 2000/1 FastFit 1CT/8
EAN/UPC - Product	8718696679449

MSR Gold™ FastFit


Order code	928410105114
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	928410105114

Net Weight (Piece)	138.000 g
--------------------	-----------

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	O	L (min)	L	L	C (max)	F
MSR Gold™ 2000/1	34 mm	8 mm	66 mm	68 mm	67 mm	134 mm	50 mm
FastFit 1CT/8							

MSR Gold 2000/1 FastFit

