



MASTER HPI-T Plus

MASTER HPI-T Plus 250W/645 E40 1SL/12

Quartz metal halide lamps with clear outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information					
Cap-Base	E40				
Operating Position	P20 [Parallel +/-20D or Horizontal(HOR)]				
Life to 50% Failures (Nom)	20,000 h				
Light Technical					
Color Code	645 [CCT of 4500K]				
Color Designation	Cool White (CW)				
Chromaticity Coordinate X (Nom)	365				
Chromaticity Coordinate Y (Nom)	377				
Correlated Color Temperature (Nom)	4500 K				
Luminous Efficacy (rated) (Nom)	79 lm/W				
Color rendering index (CRI)	65				
Arc Length O (Nom)	29 mm				
Operating and Electrical					
Power Consumption	247 W				
Voltage (Nom)	128 V				

Voltage (Nom)	128 V				
Controls and Dimming					
Dimmable	No				
Mechanical and Housing					
Bulb Finish	Clear				
Bulb Shape	T46				
Approval and Application					
Mercury (Hg) Content (Nom)	36 mg				
Energy Consumption kWh/1000 h	272 kWh				
Product Data					
Order product name	MASTER HPI-T Plus 250W/645 E40 1SL/12				
Full product name	MASTER HPI-T Plus 250W/645 E40 1SL/12				
Full product code	871150017989015				
Local code description	HPITPLUS250WGES				


Datasheet, 2023, April 14 data subject to change

MASTER HPI-T Plus

Order code	928481300098
Material Nr. (12NC)	928481300098
Local order code	HPITPLUS250WGES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500179890


Numerator - Packs per outer box	12
EAN/UPC - Case	8711500182975


Dimensional drawing




Product	D (max)	0	L	C (max)
MASTER HPI-T Plus 250W/645 E40 1SL/12	47 mm	29 mm	155 mm	255 mm

Photometric data









Light Distribution Diagram - MASTER HPI-T Plus 250W/645 E40 1SL/12

Spectral Power Distribution Colour - MASTER HPI-T Plus 250W/645 E40 1SL/12

Lifetime





Life Expectancy Diagram - MASTER HPI-T Plus 250W/645 E40 1SL/12

Lumen Maintenance Diagram - MASTER HPI-T Plus 250W/645 E40 1SL/12

MASTER HPI-T Plus



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.