

Lighting

PHILIPS

MHN-TD

MHN-TD 70W/730 RX7s 1CT/12

Double-ended quartz Metal-halide lamp

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- \cdot The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical		
Cap-Base	RX7s	Power Consumption	77.0 W	
Operating Position	P45 [Parallel +/-45D or Horizontal(HOR)]	Voltage (Nom)	90 V	
Flux measurement reference	Sphere	Voltage (Nom)	90 V	
Life to 50% Failures (Nom)	9,000 hour(s)			
		Controls and Dimming		
Light Technical		Dimmable	No	
Color Code	730 [CCT of 3000K]			
Luminous Flux	5,800 lm	Mechanical and Housing		
Color Designation	Warm White (WW)	Bulb Finish	Clear	
Chromaticity Coordinate X (Nom)	0.434	Bulb Shape	TD	
Chromaticity Coordinate Y (Nom)	0.398			
Correlated Color Temperature (Nom)	3000 K	Approval and Application		
Luminous Efficacy (Rated) (Min)	67 lm/W	Energy Efficiency Class	G	
Luminous Efficacy (rated) (Nom)	75 lm/W	Mercury (Hg) Content (Max)	13.4 mg	
Color rendering index (CRI)	65	Mercury (Hg) Content (Nom)	13.4 mg	
Arc Length O (Nom)	7.7 mm	Energy Consumption kWh/1000 h	77 kWh	

MHN-TD

EPREL Registration Number	473286		
Product Data			
Order product name	MHN-TD 70W/730 RX7s 1CT/12		
Full product name	MHN-TD 70W/730 RX7s 1CT/12		
Full product code	871829121530100		
Order code	21530100		

Material Nr. (12NC)	928482400092
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291215301
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291215318

Dimensional drawing



Product	D (max)	D	0	C (max)
MHN-TD 70W/730 RX7s 1CT/12	19.5 mm	0.75 inch	7.7 mm	117.6 mm

Photometric data





Light Distribution Diagram - MHN-TD 70W/730 RX7s 1CT/12



Spectral Power Distribution Colour - MHN-TD 70W/730 RX7s 1CT/12



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 16 - data subject to change