



MHN-TD 雙頭複金屬燈

MHN-TD 150W/730 RX7s 1CT/12

雙端型石英複金屬燈

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	RX7s
操作位置	P45 [平行 +/-45D 或水平 (HOR)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	10,500 h
照明技術	
色碼	730 [CCT of 3000K]
光通量	13,400 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.434
色度坐標 Y (Nom)	0.398
相關色彩溫度 (規範)	3000 K
流明功能 (額定) (最小)	81 lm/W
光效 (額定) (標準)	90 lm/W
演色性指數 (CRI)	67
電弧長 O (標稱)	17.8 mm


運轉與電力	
耗電量	155.0 W
電壓 (標稱)	96 V
電壓 (標稱)	96 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	TD
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	18 mg
汞 (Hg) 含量 (標稱)	18 mg
能源消耗 kWh/1000 h	155 kWh

MHN-TD 雙頭複金屬燈

EPREL 註冊碼	473287
產品資料	
下訂產品名稱	MHN-TD 150W/730 RX7s 1CT/12
完整產品名稱	MHN-TD 150W/730 RX7s 1CT/12
完整產品代碼	871829121534900
訂單代碼	928482500092



材質 Nr. (12NC)	928482500092
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718291215349
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8718291215356

二维绘图



Product	D (max)	D	O	C (max)
MHN-TD 150W/730 RX7s 1CT/12	23.0 mm	0.89 in	17.8 mm	135.4 mm

光度数据



Light Distribution Diagram - MHN-TD 150W/730 RX7s 1CT/12

Spectral Power Distribution Colour - MHN-TD 150W/730 RX7s 1CT/12

