



Mercury Vapor Standard

HPL-N 400W E39/41 HG.SLV/6

Mercury Vapor lamps feature low initial cost, but have higher operating costs than HPS or Metal Halide due to its lower efficiency. The clear mercury bulb has a bluish green appearance and the Deluxe White has a higher color rendering. Mercury lamps get dimmer over time and rarely burn out, so it is wise to replace them and restore light level.

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Color rendering index (CRI)	
Cap-Base	E39 [Single Contact Mogul Screw]		50
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	15,000 hour(s)	Power Consumption	400 W
Light Technical		Voltage (Nom)	140 V
Color Code	542 [CCT of 4200K]	Voltage (Nom)	140 V
Color Designation	Cool White (CW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	376	Dimmable	No
Chromaticity Coordinate Y (Nom)	385	Mechanical and Housing	
Correlated Color Temperature (Nom)	4200 K	Bulb Finish	Coated glass
Luminous Efficacy (rated) (Nom)	53 lm/W	Bulb Material	Hard Glass

Mercury Vapor Standard

Bulb Shape	ED120 [ED 120mm]
Approval and Application	
Mercury (Hg) Content (Nom)	72 mg
Product Data	
Order product name	HPL-N 400W E39/41 HG.SLV/6
Full product name	HPL-N 400W E39/41 HG.SLV/6


Order code	928485300091
Material Nr. (12NC)	928485300091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677248420
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677248425

Dimensional drawing



Product	D (max)	C (max)
HPL-N 400W E39/41 HG.SLV/6	122 mm	290 mm


Photometric data




Spectral Power Distribution Colour - HPL-N 400W E39/41 HG.SLV/6

Mercury Vapor Standard

Lifetime



Life Expectancy Diagram - HPL-N 400W E39/41 HG.SLV/6



Lumen Maintenance Diagram - HPL-N 400W E39/41 HG.SLV/6

