



Pulse Start Metal Halide Standard

MH 70W/640 E26 CL 1SL/24

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Voltage (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		85 V
Operating Position	H [Hanging or Base Up (BU)]	Voltage (Nom)	85 V
Life to 50% Failures (Nom)	12,000 hour(s)	Controls and Dimming	
Light Technical		Dimmable	No
Color Code	640 [CCT of 4000K]	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Finish	Clear
Chromaticity Coordinate X (Nom)	385	Bulb Shape	ED17
Chromaticity Coordinate Y (Nom)	390	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	12 mg
Luminous Efficacy (rated) (Nom)	80 lm/W	Product Data	
Color rendering index (CRI)	60	Order product name	MH 70W/640 E26 CL 1SL/24
Operating and Electrical		Full product name	MH 70W/640 E26 CL 1SL/24
Power Consumption	70.0 W		

Pulse Start Metal Halide Standard

Order code	137505
Material Nr. (12NC)	928485800191
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677137502

Numerator - Packs per outer box	24
EAN/UPC - Case	50046677137507

Dimensional drawing



Product	D (max)	L (min)	C (max)
MH 70W/640 E26 CL 1SL/24	56 mm	83 mm	138 mm

