



# **Ceramalux ALTO**

# SON ALTO 100W LV E E39 CL SL/3

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

#### **Warnings and Safety**

- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

#### **Product data**

General Information		
Cap-Base	E39 [Single Contact Mogul Screw]	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Features	ALTO® (ALTO)	
Light Technical		
Chromaticity Coordinate X (Nom)	520	
Chromaticity Coordinate Y (Nom)	420	
Correlated Color Temperature (Nom)	2100 K	
Luminous Efficacy (Rated) (Min)	85 lm/W	
Luminous Efficacy (rated) (Nom)	94 lm/W	
Color rendering index (CRI)	18	
Operating and Electrical		
Power Consumption	100.4 W	
Lamp Current (Nom)	2.1 A	
Voltage (Nom)	55 V	
Voltage (Nom)	55 V	

Mechanical and Housing		
Bulb Finish	Clear	
Bulb Material	Hard Glass	
Bulb Shape	ED-23 1/2	
Approval and Application		
Mercury (Hg) Content (Max)	22.1 mg	
Product Data		
Order product name	C100S54 3PK	
Full product name	SON ALTO 100W LV E E39 CL SL/3	
Order code	140953	
Material Nr. (12NC)	928601139806	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	046677253813	
Numerator - Packs per outer box	3	
EAN/UPC - Case	50046677140958	

Datasheet, 2023, April 24 data subject to change

## **Ceramalux ALTO**

### Dimensional drawing

Product	D	C (max)
C100S54 3PK	75 mm	196 mm





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.