



# Ceramalux Non-ALTO

## C70S62/M PH 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	522
Chromaticity Coordinate Y (Nom)	425
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	13
Operating and Electrical	
Power Consumption	70.2 W
Lamp Current (Nom)	1.6 A
Voltage (Nom)	52 V
Voltage (Nom)	52 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Soft Glass
Bulb Shape	BD17
Approval and Application	
Mercury (Hg) Content (Max)	17 mg
Product Data	
Order product name	C70S62/M PH 12PK
Full product name	C70S62/M PH 12PK
Order code	467282
Material Nr. (12NC)	928601144190
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467289
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467284

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
C70S62/M PH 12PK	2-3/16 inch	5-7/16 inch

