

# PHILIPS

## Lighting



# Switch Start Metal Halide Protected

## MP360/BU/EW 6PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

### Product data

General Information	
Cap-Base	EX39 [ Exclusionary Mogul Screw]
Operating Position	Universal [ Universal]
Main Application	General Lighting (G)
Life to 50% Failures (Nom)	20000 h
ANSI Code HID	M165/M59/O

Light Technical	
Color Code	640 [ CCT of 4000K]
Luminous Flux (Rated) (Nom)	36000 lm
Color Designation	Cool White (CW)
Design Mean Lumens	23400 lm
Chromaticity Coordinate X (Nom)	385
Chromaticity Coordinate Y (Nom)	390
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Rendering Index (Nom)	65

Operating and Electrical	
Lamp Current (Nom)	3.25 A
Ignition Supply Voltage (Min)	280 V
Re-Ignition Time (Min) (Max)	15 min

Ignition Time (Max)	
Ignition Time (Max)	120 s
Voltage (Max)	130 V
Voltage (Min)	110 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	Nic/Brass [ Nickel/Brass Base]
Bulb Material	Hard Glass

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	116 pg/lm.h
Mercury (Hg) Content (Nom)	48 mg

UV	
Pet (Niosh) (Nom)	1557 h/500lx
Damage Factor D/fc (Nom)	0.21

Luminaire Design Requirements	
Bulb Temperature (Max)	400 °C


## Switch Start Metal Halide Protected

Cap-Base Temperature (Max)	210 °C
<b>Product Data</b>	
Order product name	MP360/BU/EW 6PK
EAN/UPC - Product	046677130671
Order code	130674

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928601179201
Net Weight (Piece)	0.001 kg

### Warnings and Safety

### Dimensional drawing



#### Product

MP360/BU/EW 6PK

MP 360W/640 EX39 BT37 U ES

