

PHILIPS

Lighting



Switch Start Metal Halide Protected

MP360/BU/EW 6PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Product data

General Information		Ignition Time (Max)	
Base	EX39 [Exclusionary Mogul Screw]		120 s
Operating Position	Universal [Universal]	Voltage (Max)	130 V
Main Application	General Lighting (G)	Voltage (Min)	110 V
Life to 50% Failures (Nom)	20000 h	Voltage (Nom)	120 V
ANSI Code HID	M165/M59/O		
Light Technical		Mechanical and Housing	
Color Code	640 [CCT of 4000K]	Bulb Finish	Clear
Luminous Flux (Rated) (Nom)	36000 lm	Cap-Base Information	Nic/Brass
Color Designation	Cool White (CW)	Bulb Material	Hard Glass
Design Mean Lumens	23400 lm	Approval and Application	
Chromaticity Coordinate X (Nom)	385	Energy Saving Product	Energy Saving
Chromaticity Coordinate Y (Nom)	390	Picogram Per Lumen Hour	116 pg/lm.h
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	48 mg
Luminous Efficacy (rated) (Nom)	100 lm/W	UV	
Color Rendering Index (Nom)	65	Pet (Niosh) (Nom)	1557 h/500lx
		Damage Factor D/fc (Nom)	0.21
Operating and Electrical		Luminaire Design Requirements	
Lamp Current (Nom)	3.25 A	Bulb Temperature (Max)	400 °C
Ignition Supply Voltage (Min)	280 V		
Re-Ignition Time (Min) (Max)	15 min		


Switch Start Metal Halide Protected

Cap-Base Temperature (Max)	210 °C
Product Data	
Order product name	MP360/BU/EW 6PK
EAN/UPC - Product	046677130671
Order code	130674

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928601179201
Net Weight (Piece)	0.001 kg

Warnings and Safety

Dimensional drawing



Product

MP360/BU/EW 6PK

MP 360W/640 EX39 BT37 U ES

