



# Switch Start Metal Halide Standard

## MH150/U/M 12PK

High performance, Long life and Superior light quality A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	General Lighting (G)
Life to 50% Failures (Nom)	10000 h
ANSI Code HID	M57/E

Light Technical	
Color Code	640 [ CCT of 4000K]
Luminous Flux (Rated) (Nom)	13500 lm
Color Designation	White (WH)
Lumen Maintenance - 40% Life	65 %
Design Mean Lumens	8775 lm
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.390
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Rendering Index (Nom)	65

Operating and Electrical	
Lamp Current (Nom)	1.5 A

Ignition Supply Voltage (Min)	250 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	120 s
Voltage (Max)	120 V
Voltage (Min)	100 V
Voltage (Nom)	110 V

Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	Brass [ Brass Cap]
Bulb Material	Hard Glass

Approval and Application	
Energy Saving Product	Not Applicable
Picogram Per Lumen Hour	199.4 pg/lm.h
Mercury (Hg) Content (Nom)	23 mg

UV	
Pet (Niosh) (Nom)	133.1 h/500lx
Damage Factor D/fc (Nom)	0.54

## Switch Start Metal Halide Standard

### Luminaire Design Requirements

Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	210 °C


### Product Data

Order product name	MH150/U/M 12PK
EAN/UPC - Product	046677354626

Order code	354621
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601179801
Net Weight (Piece)	0.001 kg

## Warnings and Safety

### Dimensional drawing



MH R 150W/640 E26 ED17 CL U

### Product

MH150/U/M 12PK

