

Xitanium LED Driver

Indoor Linear

Dimmable (US)

XITANIUM 54W 0.1-1.5A 27-54V 0-10V INT-T

Xitanium Indoor LED Drivers are available in a wide variety of wattages up to 75W. Most models include adjustable output current to enable OEMs to set LED drive current specific to their needs. These drivers are available in form factors perfectly suited for indoor linear troffer applications. 1-10V and leading edge dimming options enable energy-efficient solutions.

Product data

General Information	
Lighting Technology	LED
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Total Harmonic Distortion IEC (Max)	20 %
Power Consumption	61 W
Maximum Efficiency at Full Load	86/88 %
Output Current (Max)	1500 mA
Output Current (Nom)	700-1500 mA
Input Current (Max)	540 mA
Output Power (Max)	54 W
Output Power (Nom)	54 W
Output Power (Min)	0 W
Output Current (Min)	100 mA
Output Voltage (Max)	54 V


Output Voltage (Min)	27 V
Wiring	
Primary Fusing	Fused
Temperature	
Ambient temperature range	-4 °F to 122 °F
T-Case Maximum (Max)	185 °F
Controls and Dimming	
Dimmable	Yes
Control Interface	0-10V
Dimming Range	100-5 %
Constant light output	No
Approval and Application	
Short Circuit Protection	Protected

Xitanium LED Driver Indoor Linear Dimmable (US)

EMI Standard	FCC Title 47 Part 15; Class B
Environmental Standard	UL Damp & Dry
Approval Marks	RoHS compliance CSA certificate
Product Data	
Order product name	XITANIUM 54W 0.1-1.5A 27-54V 0-10V INT-T
Full product name	XITANIUM 54W 0.1-1.5A 27-54V 0-10V INT-T
Full product code	871869690027700

Order code	929000711113
Material Nr. (12NC)	929000711113
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	781087130254
Numerator - Packs per outer box	18
EAN/UPC - Case	50781087130266

Dimensional drawing



Product	C1	A1	A2	B1
XITANIUM 54W 0.1-1.5A 27-54V 0-10V INT-T	1 inch	14-1/8 inch	13-13/16 inch	1-3/16 inch

