



# Xitanium LED Driver Outdoor Dimmable (US)

## Xitanium 150W 120-277V 1.05A 0-10V

Xitanium Outdoor LED Drivers are available in wattages from 40W to 150W for hard-wire integration into outdoor luminaires for the most rugged applications. These drivers operate to specification under wide temperature and electrical ranges to ensure reliability. 1-10V dimming enables luminaires to be easily connected to a wide variety of sensors and control systems to facilitate dimming, thus maximizing energy savings.

### Product data

| General Information                 |             |
|-------------------------------------|-------------|
| Lighting Technology                 | LED         |
| Operating and Electrical            |             |
| Line Frequency                      | 50 to 60 Hz |
| Input Frequency                     | 50 to 60 Hz |
| Total Harmonic Distortion IEC (Max) | 20 %        |
| Power Consumption                   | 167 W       |
| Output Current (Nom)                | 1050 mA     |
| Output Current Tolerance (Max)      | 5 %         |
| Output Current Tolerance (Min)      | -5 %        |
| Output Power (Nom)                  | 150 W       |
| Wiring                              |             |
| Primary Fusing                      | Fused       |


| Input Wire Gauge         | 18                      |
|--------------------------|-------------------------|
| Temperature              |                         |
| T-Case Maximum (Max)     | 80 °C                   |
| Controls and Dimming     |                         |
| Control Interface        | 0-10V                   |
| Dimming Range            | 100-10 %                |
| Approval and Application |                         |
| Overheating Protection   | Protected               |
| Short Circuit Protection | Self-limited            |
| Over Power Protection    | Protected               |
| Open Circuit Protection  | Protected               |
| EMI Standard             | FCC 47 Part 15; Class A |
| Environmental Standard   | UL Damp & Dry           |

Xitanium LED Driver Outdoor Dimmable (US)

|                     |                                                |
|---------------------|------------------------------------------------|
| Approval Marks      | RoHS compliance UL certificate CSA certificate |
| Product Data        |                                                |
| Order product name  | Xitanium 150W 120-277V 1.05A 0-10V             |
| Full product name   | Xitanium 150W 120-277V 1.05A 0-10V             |
| Order code          | 929000722913                                   |
| Material Nr. (12NC) | 929000722913                                   |

|                                 |                |
|---------------------------------|----------------|
| Numerator - Quantity Per Pack   | 1              |
| EAN/UPC - Product/Case          | 781087135723   |
| Numerator - Packs per outer box | 10             |
| EAN/UPC - Case                  | 50781087135735 |

Dimensional drawing



| Product                                  | D1     | B2      | C1      | C2      | A1       | A2       | B1      |
|------------------------------------------|--------|---------|---------|---------|----------|----------|---------|
| Xitanium 150W<br>120-277V 1.05A<br>0-10V | 4.8 mm | 42.9 mm | 39.7 mm | 37.7 mm | 240.5 mm | 241.5 mm | 59.1 mm |

