



Xitanium LED Driver Outdoor Fixed (US)

XITANIUM 150W 0.70A 210V 347-480V

Xitanium Outdoor LED Drivers are available in wattages from 40W to 150W for hard-wire integration into outdoor luminaires for the most rugged applications. These drivers operate to specification under wide temperature and electrical ranges to ensure reliability.

Product data

General Information	
Lighting Technology	LED
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Total Harmonic Distortion IEC (Max)	20 %
Power Consumption	167 W
Maximum Efficiency at Full Load	90 %
Output Current (Nom)	350 mA
Output Current Tolerance (Max)	5 %
Output Current Tolerance (Min)	-5 %
Input Current (Max)	500 mA
Output Power (Nom)	150 W
Wiring	
Connector Type Input Terminals	Wago 250
Primary Fusing	Fused
Input Wire Gauge	18

Temperature	
T-Case Maximum (Max)	80 °C
Approval and Application	
Short Circuit Protection	Self-limited
Over Power Protection	Protected
Open Circuit Protection	Protected
Environmental Standard	UL Damp & Dry
Approval Marks	RoHS compliance UL certificate CSA certificate
Product Data	
Order product name	XITANIUM 150W 0.70A 210V 347-480V
Full product name	XITANIUM 150W 0.70A 210V 347-480V
Order code	929000727313
Material Nr. (12NC)	929000727313
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	781087138069
Numerator - Packs per outer box	10
EAN/UPC - Case	50781087138071

Xitanium LED Driver Outdoor Fixed (US)

Dimensional drawing

Product	A1	A2	B1	C1
XITANIUM 150W 0.70A 210V 347-480V	240.5 mm	226.2 mm	59.1 mm	37 mm

