



Essential LED tubes T5 Mains

MASTER LEDtube 1200mm 13W840 G5 I

The Essential LEDtube T5 is an affordable LED solution suitable for replacing T5 fluorescent lamps. Thanks to a unique design, Philips Essential LED tube T5 Mains can be directly installed in luminaires operating on mains power connection. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information		Input Frequency	
Cap-Base	G5 [G5]	Power Consumption	13 W
Nominal lifetime	40,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	33 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	160 degree(s)	T-Case Maximum (Nom)	50 °C
Luminous Flux	1,600 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	123.00 lm/W	Product Length	1,200 mm
Color Consistency	<6	Bulb Shape	T5
Color rendering index (CRI)	83	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Essential LED tubes T5 Mains


Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate CE marking
Energy Consumption kWh/1000 h	15 kWh

Product Data

Order product name	MASTER LEDtube 1200mm 13W840 G5 I
Full product name	MASTER LEDtube 1200mm 13W840 G5 I
Full product code	694793910873200


Order code	10873200
Material Nr. (12NC)	929001131110
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939108732
Numerator - Packs per outer box	20
EAN/UPC - Case	6947939108749

Dimensional drawing




Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm 13W840 G5 I	15.8 mm	21.0 mm	1,148.0 mm	1,155.0 mm	1,162.0 mm

Photometric data




Light Distribution Diagram - MASTER LEDtube 1200mm 13W840 G5 I



General uniform lighting - MASTER LEDtube 1200mm 13W840 G5 I

Essential LED tubes T5 Mains

Photometric data



Spectral Power Distribution Colour - MASTER LEDtube 1200mm 13W840 G5
I

