



# MASTER LEDspot LV

## MASTER LED 5.5-50W 3000K MR16 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Product data

General Information	
Cap-Base	GU5.3 [ GU5.3]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	5.5-50W
Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	24 °
Luminous Flux (Nom)	425 lm
Luminous Intensity (Nom)	1800 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	77.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Power (Rated) (Nom)	5.5 W
Lamp Current (Nom)	640 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No

# MASTER LEDspot LV

## Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes


## Product Data

Full product code	871869647607900
Order product name	MASTER LED 5.5-50W 3000K MR16 24D
EAN/UPC - Product	8718696476079

Order code	929001146708
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001146708
Net Weight (Piece)	0.035 kg

## Warnings and Safety


### Dimensional drawing




MR16 12V 5.5W-50W 380lm 3000K GU5.3 ND

Product	D	C
MASTER LED 5.5-50W 3000K MR16 24D	50.2 mm	49 mm

### Photometric data



MASTER LED 5.5-50W MR16 GU5.3 3000K 425lm 24D



MASTER LED 5.5-50W MR16 GU5.3 3000K 425lm 24D

# MASTER LEDspot LV

