



# MASTER VALUE LEDspot LV

## MASTER LED 5.5-50W 4000K MR16 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information			
Cap-Base	GU5.3	Beam Angle (Nom)	36 degree(s)
Nominal lifetime	25,000 hour(s)	Luminous Flux	450 lm
Switching Cycle	50,000	Luminous Intensity (Nom)	1,000 cd
Lighting Technology	LED	Color Designation	Cool White (CW)
EU RoHS compliant	Yes	Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	82.00 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	80
Light Technical			
Color Code	840 [CCT of 4000K]		

MASTER VALUE LEDspot LV

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical

Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	5.5 W
Lamp Current (Nom)	640 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	MR16
------------	------


Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

Product Data


Order product name	MASTER LED 5.5-50W 4000K MR16 36D
Full product name	MASTER LED 5.5-50W 4000K MR16 36D
Full product code	871869647611600
Order code	47611600
Material Nr. (12NC)	929001146908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476116
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476123

Dimensional drawing




Product	D	C
MASTER LED 5.5-50W 4000K MR16 36D	50.2 mm	49 mm

Photometric data



General uniform lighting - MASTER LED 5.5-50W 4000K MR16 36D



Light Distribution Diagram - MASTER LED 5.5-50W 4000K MR16 36D

## MASTER VALUE LEDspot LV

