



MASTER VALUE LEDspot pot LV

MASTER LED 4-35W 2700K MR16 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information		EU RoHS compliant	
Cap-Base	GU5.3 [GU5.3]		Yes
Nominal lifetime	25,000 hour(s)	Light Technical	
Switching Cycle	50,000	Color Code	827 [CCT of 2700K]
Lighting Technology	LED	Beam Angle (Nom)	36 degree(s)

MASTER VALUE LEDspot LV

Luminous Flux	240 lm
Luminous Intensity (Nom)	550 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	65.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	220 lm

Operating and Electrical

Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	4 W
Lamp Current (Nom)	520 mA
Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	65 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	MR16 [2inch/50mm]
------------	-------------------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

Product Data

Order product name	MASTER LED 4-35W 2700K MR16 36D
Full product name	MASTER LED 4-35W 2700K MR16 36D
Full product code	871869647621500
Order code	929001147508
Material Nr. (12NC)	929001147508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476215
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476222


Dimensional drawing




Product	D	C
MASTER LED 4-35W 2700K MR16 36D	50 mm	49 mm

MASTER VALUE LEDspot LV

Photometric data



Light Distribution Diagram - MASTER LED 4-35W 2700K MR16 36D



Spectral Power Distribution Colour - MASTER LED 4-35W 2700K MR16 36D

