



MASTER LEDbulb

MASTER LEDbulb DT 8.5-60W E27 A60 CL

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

Product data

General Information		Temperature	
Cap base	E27 [E27]	Lamp current (nom.)	45 mA
EU RoHS compliant	Yes	Wattage equivalent	60 W
Nominal lifetime (nom.)	25000 h	Starting time (nom.)	0.5 s
Switching cycle	50000X	Warm-up time to 60% light (nom.)	0.5 s
Technical type	8.5-60W	Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Colour code	822-827 [tunable warm white]	Dimmable	Yes
Luminous flux (nom.)	806 lm		
Colour designation	Warm white (WW)	Mechanical and Housing	
Luminous efficacy (rated) (nom.)	94 lm/W	Bulb finish	Clear
Colour consistency	<6		
Color rendering index (nom.)	80	Approval and Application	
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A+
		Energy-saving product	Yes
Operating and Electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	8.5 W		

MASTER LEDbulb


Suitable for accent lighting	No
Energy Consumption kWh/1000 h	9 kWh

Product Data

Full product code	871869648132500
Order product name	MASTER LEDbulb DT 8.5-60W E27 A60 CL
EAN/UPC – product	8718696481325

Order code	48132500
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001150932
Net weight (piece)	0.076 kg

Dimensional drawing



LED DT 9-60W E27 A60 CL

Product	D	C
MASTER LEDbulb DT 8.5-60W E27 A60 CL	60 mm	110 mm

Photometric data

