



CorePro LED PLC 4P

CorePro LED PLC 9W 830 4P G24q-3

The CorePro LED PLC 4P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data


General Information			
Cap-Base	G24q-3	Input Frequency	30000-80000 Hz
Nominal lifetime	30,000 hour(s)	Power Consumption	9 W
Switching Cycle	50,000	Lamp Current (Max)	400 mA
Lighting Technology	LED	Lamp Current (Min)	250 mA
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
CE mark	Yes	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.9
		Voltage (Nom)	20-50 V
		LED alternative to fluorescent lamp power	26 W
		Inrush current at mains	-
		Max. lamp no. on MCB B type 10A - Mains	-
		Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	-
		Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	-
		Max. lamp no. on MCB B type 16A - Mains	-
		Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	-
		Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	-
		Ballast Compatibility	HF
Light Technical			
Color Code	830 [CCT of 3000K]		
Beam Angle (Nom)	120 degree(s)		
Luminous Flux	950 lm		
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	100.00 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	83		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Photobiological safety according to EN 62471	RG0		
Operating and Electrical			
Line Frequency	30000-80000 Hz		

CorePro LED PLC 4P

Temperature	
Ambient temperature range	-20 °C to 35 °C
T-Case Maximum (Nom)	76 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Plastic
Product Length	200 mm
Bulb Shape	PL-C
Approval and Application	
Energy Efficiency Class	F
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	9 kWh



EPREL Registration Number	403550
Product Data	
Order product name	CorePro LED PLC 9W 830 4P G24q-3
Full product name	CorePro LED PLC 9W 830 4P G24q-3
Full product code	871869654115900
Order code	929001200802
Material Nr. (12NC)	929001200802
Local order code	LPLC9W8304P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696541159
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696541166

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLC 9W 830 4P G24q-3	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm

Photometric data



General uniform lighting - CorePro LED PLC 9W 830 4P G24q-3

Light Distribution Diagram - CorePro LED PLC 9W 830 4P G24q-3


CorePro LED PLC 4P

Photometric data




Spectral Power Distribution Colour - CorePro LED PLC 9W 830 4P G24q-3


Lifetime




Life Expectancy Diagram - CorePro LED PLC 9W 830 4P G24q-3



Life Expectancy Diagram - CorePro LED PLC 9W 830 4P G24q-3




Life Expectancy Diagram - CorePro LED PLC 9W 830 4P G24q-3



Lumen Maintenance Diagram - CorePro LED PLC 9W 830 4P G24q-3

CorePro LED PLC 4P

Lifetime



Lumen Maintenance Diagram - CorePro LED PLC 9W 830 4P G24q-3

