



CorePro LED PLC 4P

CorePro LED PLC 9W 840 4P G24q-3

The CorePro LED PLC 4P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data


General Information		Input Frequency	
Cap-Base	G24q-3	Power Consumption	30000-80000 Hz
Nominal lifetime	30,000 hour(s)	Lamp Current (Max)	9 W
Switching Cycle	50,000	Lamp Current (Min)	400 mA
Lighting Technology	LED	Starting Time (Nom)	250 mA
Flux measurement reference	Sphere	Warm-up time to 60% light	0.5 s
CE mark	Yes	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	20-50 V
Light Technical		LED alternative to fluorescent lamp power	26 W
Color Code	840 [CCT of 4000K]	Inrush current at mains	-
Beam Angle (Nom)	120 degree(s)	Max. lamp no. on MCB B type 10A - Mains	-
Luminous Flux	1,000 lm	Max. lamp no. on MCB B type 10A - EM ballast without Comp. Cap.	-
Color Designation	Cool White (CW)	Max. lamp no. on MCB B type 10A - EM ballast with Comp. Cap.	-
Correlated Color Temperature (Nom)	4000 K	Max. lamp no. on MCB B type 16A - Mains	-
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Max. lamp no. on MCB B type 16A - EM ballast without Comp. Cap.	-
Color Consistency	<6	Max. lamp no. on MCB B type 16A - EM ballast with Comp. Cap.	-
Color rendering index (CRI)	83	Ballast Compatibility	HF
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Photobiological safety according to EN 62471	RG0		
Operating and Electrical			
Line Frequency	30000-80000 Hz		

CorePro LED PLC 4P

Temperature	
Ambient temperature range	-20 °C to 35 °C
T-Case Maximum (Nom)	76 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	200 mm
Bulb Shape	PL-C
Approval and Application	
Energy Efficiency Class	F
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	9 kWh



EPREL Registration Number	403551
Product Data	
Order product name	CorePro LED PLC 9W 840 4P G24q-3
Full product name	CorePro LED PLC 9W 840 4P G24q-3
Full product code	871869654117300
Order code	54117300
Material Nr. (12NC)	929001200902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696541173
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696541180

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLC 9W 840 4P G24q-3	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm

Photometric data




General uniform lighting - CorePro LED PLC 9W 840 4P G24q-3

Spectral Power Distribution Colour - CorePro LED PLC 9W 840 4P G24q-3


CorePro LED PLC 4P

Photometric data




Light Distribution Diagram - CorePro LED PLC 9W 840 4P G24q-3


Lifetime




Life Expectancy Diagram - CorePro LED PLC 9W 840 4P G24q-3



Life Expectancy Diagram - CorePro LED PLC 9W 840 4P G24q-3




Life Expectancy Diagram - CorePro LED PLC 9W 840 4P G24q-3



Lumen Maintenance Diagram - CorePro LED PLC 9W 840 4P G24q-3

CorePro LED PLC 4P

Lifetime



Lumen Maintenance Diagram - CorePro LED PLC 9W 840 4P G24q-3

