



# CorePro LED PLC 2P

## CorePro LED PLC 8.5W 840 2P G24d-3

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

### Product data

General Information	
Cap-Base	G24D-3 [G24d-3]
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	1,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105.88 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RGO

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	8.5 W
Lamp Current (Max)	43 mA
Lamp Current (Min)	33 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	26 W
Max. lamp no. on MCB B type 10A - Mains	74
Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	150
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	30
Max. lamp no. on MCB B type 16A - Mains	118
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	220
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	49


Temperature	
Ambient temperature range	-20 °C to 35 °C

CorePro LED PLC 2P

T-Case Maximum (Nom)	75 °C
<b>Controls and Dimming</b>	
Dimmable	No
<b>Mechanical and Housing</b>	
Bulb Material	Plastic
Product Length	200 mm
Bulb Shape	PL-C
<b>Approval and Application</b>	
Energy Efficiency Class	F
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	9 kWh



EPREL Registration Number	403555
<b>Product Data</b>	
Order product name	CorePro LED PLC 8.5W 840 2P G24d-3
Full product name	CorePro LED PLC 8.5W 840 2P G24d-3
Full product code	871869654125800
Order code	929001201302
Material Nr. (12NC)	929001201302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696541258
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696541265

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLC 8.5W 840 2P G24d-3	24.3 mm	28.4 mm	128.8 mm	148 mm	170.6 mm

Photometric data




General uniform lighting - CorePro LED PLC 8.5W 840 2P G24d-3

Spectral Power Distribution Colour - CorePro LED PLC 8.5W 840 2P G24d-3


CorePro LED PLC 2P

Photometric data




Light Distribution Diagram - CorePro LED PLC 8.5W 840 2P G24d-3


Lifetime




Life Expectancy Diagram - CorePro LED PLC 8.5W 840 2P G24d-3



Life Expectancy Diagram - CorePro LED PLC 8.5W 840 2P G24d-3




Life Expectancy Diagram - CorePro LED PLC 8.5W 840 2P G24d-3



Lumen Maintenance Diagram - CorePro LED PLC 8.5W 840 2P G24d-3

CorePro LED PLC 2P

Lifetime



Lumen Maintenance Diagram - CorePro LED PLC 8.5W 840 2P G24d-3

