



Classic LEDspotMV

Essential LED 4.6-50W GU10 830 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

Product data

General Information		Wattage equivalent	
Cap base	GU10 [GU10]		50 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50000X	Warm-up time to 60% light (nom.)	0.5 s
Technical type	4.6-50W	Power factor (nom.)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour code	830 [CCT of 3,000 K]	T-Case maximum (nom.)	85 °C
Beam Angle (Nom)	36 °		
Luminous flux (nom.)	410 lm	Controls and Dimming	
Luminous intensity (nom.)	740 cd	Dimmable	No
Colour designation	White (WH)		
Correlated colour temperature (nom.)	3000 K	Approval and Application	
Luminous efficacy (rated) (nom.)	89.10 lm/W	Energy efficiency label (EEL)	A+
Colour consistency	<6	Suitable for accent lighting	Yes
Color rendering index (nom.)	80	Energy Consumption kWh/1000 h	5 kWh
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical		Product Data	
Input frequency	50 to 60 Hz	Full product code	871869671342600
Power (Rated) (Nom)	4.6 W	Order product name	Essential LED 4.6-50W GU10 830 36D
Lamp current (nom.)	39 mA	EAN/UPC – product	8718696713426
		Order code	71342600

Classic LEDspotMV

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001218108

Net weight (piece)	0.038 kg
--------------------	----------



Dimensional drawing



GU10 230V 4W-35W 260lm 100D 2700K GU10ND


Product	D	C
Essential LED 4.6-50W GU10 830 36D	50 mm	54 mm

Photometric data



LEDspot,PAR38 11W 900lm 3000K

CorePro LEDspotMV 50W GU10 830 36D CLA




CorePro LEDspotMV 50W GU10 830 36D CLA

Classic LEDspotMV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND



CLA LEDspotMV 50W GU10 827 36D ND

