

# Classic filament LEDbulbs

## LEDClassic 7-60W G120 E27 2000K GOLD APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7-60W

Light Technical	
Colour Code	820 [ CCT of 2,000 K]
Lamp Luminous Flux 25°C EL (Nom)	630 lm
Colour Designation	Flame
Colour Temperature, horizontal (Nom)	2000 K
Lamp Luminous Efficacy EM (Nom)	90.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W
Lamp current (nom.)	40 mA

Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Gold Clear

Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	7 kWh


Product Data	
Full product code	871869657493500

# Classic filament LEDbulbs

Order product name	LEDClassic 7-60W G120 E27 2000K GOLD APR
EAN/UPC – product	8718696574935
Order code	929001229108
Numerator – quantity per pack	1
Numerator – packs per outer box	6

Material no. (12NC)	929001229108
Net weight (piece)	0.115 kg


## Dimensional drawing




filament 7W-60W 620lm NAD 2200K E27D

Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm


## Photometric data



LED Lamps, Lightcolour /820 ST64 GOLD



Classic LEDBulb D 7-50W G120 820 GOLD



Classic LEDBulb D 7-50W G120 820 GOLD

## Classic filament LEDbulbs

