



Classic filament LEDbulbs

LEDClassic 7-60W G120 E27 2000K GOLD APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)		40 mA
Cap-Base	E27 [E27]	Wattage Equivalent		60 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	20,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)		0.7
Lighting Technology	LED	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	820 [CCT of 2000K]	T-Case Maximum (Nom)		70 °C
Luminous Flux	630 lm	Controls and Dimming		
Color Designation	Flame	Dimmable		Yes
Correlated Color Temperature (Nom)	2000 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Finish		Gold Clear
Color Consistency	<6	Bulb Shape		G120 [G 120mm]
Color rendering index (CRI)	80	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product		Yes
Operating and Electrical		Suitable For Accent Lighting		No
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h		7 kWh
Input Frequency	50 to 60 Hz			
Power Consumption	7 W			

Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 7-60W G120 E27 2000K GOLD APR
Full product name	LEDClassic 7-60W G120 E27 2000K GOLD APR
Full product code	871869657493500
Order code	929001229108


Material Nr. (12NC)	929001229108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574935
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574942

Dimensional drawing




Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 7-60W G120 E27 2000K GOLD APR



General uniform lighting - LEDClassic 7-60W G120 E27 2000K GOLD APR



Light Distribution Diagram - LEDClassic 7-60W G120 E27 2000K GOLD APR

Classic filament LEDbulbs

