



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 2-20W G4 827 D

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data

General Information	
Cap base	G4 [G4]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	2-20W

Light Technical	
Colour code	827 [CCT of 2,700 K]
Luminous flux (nom.)	200 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Power (Rated) (Nom)	2 W
Lamp current (nom.)	220 mA

Wattage equivalent	20 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	12 V

Temperature	
T-Case maximum (nom.)	84 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	3 kWh


CorePro LEDcapsule LV

Product Data

Full product code	871869657865000
Order product name	CorePro LEDcapsuleLV 2-20W G4 827 D
EAN/UPC – product	8718696578650
Order code	57865000
Numerator – quantity per pack	1

Numerator – packs per outer box	12
Material no. (12NC)	929001235302
Net weight (piece)	0.012 kg


Dimensional drawing




Capsule 12V 2W-20W 200lm 2700K G4 D

Product	D	C
CorePro LEDcapsuleLV 2-20W G4 827 D	17 mm	48 mm


Photometric data



LED Lamps, CorePro LEDcapsuleLV D 2-20W G4 /827



LED Lamps, CorePro LEDcapsuleLV D 2-20W G4 /827



LED Lamps, CorePro LEDcapsuleLV D 2-20W G4 /827

CorePro LEDcapsule LV

