

# MASTER LEDspot ExpertColor LV

## MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 927 10D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

### Product data

General Information	
Cap base	GU5.3 [ GU5.3]
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Technical type	7.2-50W
Light Technical	
Colour Code	927
Beam Angle (Nom)	10°
Lamp Luminous Flux 25°C EL (Nom)	450 lm
Lamp Luminous Flux (Nom)	450 lm
Luminous intensity (nom.)	4500 cd
Colour Designation	Warm white (WW)
Rated beam angle	10°
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	62.50 lm/W

Colour consistency	<3
Colour Rendering Index,horiz (Nom)	97
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Power (Rated) (Nom)	7.2 W
Lamp current (nom.)	800 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case maximum (nom.)	92 °C

# MASTER LEDspot ExpertColor LV

## Controls and Dimming

Dimmable Yes

## Approval and Application

Energy-saving product Yes

Suitable for accent lighting Yes

## Product Data

Full product code 871869657161300  
 Order product name MASTER LED ExpertColor LED MR16  
 ExpertColor 7.2-50W 927 10D

EAN/UPC – product 8718696571613

Order code 929001241908


Numerator – quantity per pack 1

Numerator – packs per outer box 10

Material no. (12NC) 929001241908

Net weight (piece) 0.034 kg


## Dimensional drawing




MR16 12V 7.2-50W 420lm 10D 2700K GU5.3 D

Product	D	C
MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 927 10D	51 mm	46 mm

## Photometric data




MAS LED ExpertColor 7.2-50W MR16 GU5.3 927



MAS LED ExpertColor 7.2-50W MR16 GU5.3 927 10D

# MASTER LEDspot ExpertColor LV

## Photometric data



MAS LED ExpertColor 7.2-50W MR16 GU5.3 927 10D

