



MASTER LEDspot ExpertColor LV

MASTER LED MR16 ExpertColor 7.2-50W 940 10D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data

General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	GU5.3 [GU5.3]		
Nominal lifetime	40,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	940 [CCT of 4000K]	Line Frequency	- Hz
Beam Angle (Nom)	10 degree(s)	Input Frequency	- Hz
Luminous Flux	480 lm	Power Consumption	7.2 W
Luminous Intensity (Nom)	5,000 cd	Lamp Current (Nom)	800 mA
Color Designation	Cool White (CW)	Wattage Equivalent	50 W
Correlated Color Temperature (Nom)	4000 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	66.67 lm/W	Warm-up time to 60% light	1 s
Color Consistency	<3	Power Factor (Fraction)	0.7
Color rendering index (CRI)	97	Voltage (Nom)	12 V
		Temperature	
		T-Case Maximum (Nom)	92 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

Product Data	
Order product name	MAS LED MR16 ExpertColor 7.2-50W 940 10D



Full product name	MASTER LED MR16 ExpertColor 7.2-50W 940 10D
Full product code	871869657175000
Order code	57175000
Material Nr. (12NC)	929001242108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696571750
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696571767

Dimensional drawing



Product	D	C
MAS LED MR16 ExpertColor 7.2-50W 940 10D	51 mm	46 mm

Photometric data




General uniform lighting - MAS LED MR16 ExpertColor 7.2-50W 940 10D

Light Distribution Diagram - MAS LED MR16 ExpertColor 7.2-50W 940 10D

MASTER LEDspot ExpertColor LV

Photometric data



Spectral Power Distribution Colour - MAS LED MR16 ExpertColor 7.2-50W
940 10D

