



# MASTER LEDspot LV

## LED MR16 3-50W 36D 865

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

### Product data


General Information			
Cap-Base	GU5.3 [GU5.3]	Correlated Color Temperature (Nom)	6500 K
Nominal lifetime	25,000 hour(s)	Luminous Efficacy (rated) (Nom)	140.00 lm/W
Switching Cycle	50,000	Color Consistency	<6
Lighting Technology	LED	Color rendering index (CRI)	80
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	865 [CCT of 6500K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	50 to 60 Hz
Luminous Flux	420 lm	Power Consumption	3 W
Luminous Intensity (Nom)	850 cd	Lamp Current (Nom)	500 mA
Color Designation	Cool Daylight	Wattage Equivalent	50 W
		Starting Time (Nom)	0.5 s

MASTER LEDspot LV

Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.6
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	52 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes



Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LED MR16 3-50W 36D 865
Full product name	LED MR16 3-50W 36D 865
Full product code	871869667060600
Order code	67060600
Material Nr. (12NC)	929001275197
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696670606
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696670613

Dimensional drawing



Product	D	C
LED MR16 3-50W 36D 865	51 mm	46 mm

Photometric data




Spectral Power Distribution Colour - LED MR16 3-50W 36D 865

General uniform lighting - LED MR16 3-50W 36D 865

## MASTER LEDspot LV

### Photometric data



Light Distribution Diagram - LED MR16 3-50W 36D 865

