

T8

35T8/96-3000 IF FA8 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data


General Information		Voltage (Nom)	
Cap-Base	FA8 [FA8]	280-410 V	
EU RoHS compliant	Yes	Temperature	
Nominal Lifetime (Nom)	50000 h	T-Storage (Max)	65 °C
Switching Cycle	50000X	T-Storage (Min)	-40 °C
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	No
Luminous Flux (Nom)	3900 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Product Length	2400 mm
Color Consistency	<6	Approval and Application	
Color Rendering Index (Nom)	82	Energy Saving Product	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval Marks	UL certificate
Operating and Electrical		Product Data	
Input Frequency	50000-64000 Hz	Order product name	35T8/96-3000 IF FA8 10/1
Power (Nom)	35 W	EAN/UPC - Product	046677472566
Lamp Current (Max)	260 mA	Order code	929001307704
Lamp Current (Min)	160 mA		
Warm Up Time to 60% Light (Nom)	0.5 s		

T8

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001307704

Net Weight (Piece)	0.540 kg
--------------------	----------



Dimensional drawing



TLED Ess IF 4000lm 3000K 8ft single pin

Product	D	A1	A2	A3
35T8/96-3000 IF FA8 10/1	27.9 mm	2366.9 mm	2375.2 mm	2383.5 mm


Photometric data



General Lighting Layout

TLED Ess 35W FA8 830 3900lm T8



TLED Ess 35W FA8 830 3900lm T8



TLED Ess 35W FA8 830 3900lm T8

T8

Lifetime



TLED Ess 35W FA8 T8 IF

TLED Ess 35W FA8 T8 IF

