



LED PAR20

7PAR20/LED/F40/840/E26/GL/DIM 120V 6/1

Philips is driving the switch to energy-efficient solutions. Upgrade your track and accent lights with our small diameter reflectors for instant energy savings and unbeatable quality. Available in both Glass and Plastic casings, Philips LED Par20s are the ideal replacement for halogen.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	7-50W
Light Technical	
Color Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	40 °
Initial lumen (Nom)	500 lm
Luminous Intensity (Nom)	1000 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	71.43 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	7 W
Lamp Current (Nom)	70 mA

Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Suitable For Accent Lighting	Yes
Product Data	
Order product name	7PAR20/LED/F40/840/E26/GL/DIM 120V
EAN/UPC - Product	046677471156
Order code	471151
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001317004
Net Weight (Piece)	0.135 kg

LED PAR20



Dimensional drawing



PAR20 120V 6W-50W 500lm 40D 4000K E26 D


Product	D	C
7PAR20/LED/F40/840/E26/GL/DIM 120V	63 mm	85.5 mm

Photometric data



LEDlamps, MR16 8W-50W 4000K GU5.3



Classic PAR20 6W-50W 500lm 40D 4000K E26 D



LEDspot PAR20 7W 840 500lm 40D

LED PAR20

Lifetime



LEDspot PAR20 7W 500lm

LEDspot PAR20 7W 500lm

