



MASTER LEDspot PAR

MAS LEDspot D 6-50W E27 827 PAR20 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	25000 h
Technical type	6-50W
Light Technical	
Colour code	827 [CCT of 2,700 K]
Beam Angle (Nom)	25°
Luminous flux (nom.)	520 lm
Luminous intensity (nom.)	1500 cd
Colour designation	Warm White (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	86.67 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %


Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	6 W
Lamp current (nom.)	32 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.85
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes

MASTER LEDspot PAR

Energy Consumption kWh/1000 h	6 kWh
Product Data	
Full product code	871869671408900
Order product name	MAS LEDspot D 6-50W E27 827 PAR20 25D
EAN/UPC – product	8718696714089
Order code	71408900

Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001317408
Net weight (piece)	0.135 kg


Dimensional drawing




PAR20 220-240V 6W-50W 25D 2700K E26 D

Product	D	C
MAS LEDspot D 6-50W E27 827 PAR20 25D	64 mm	85 mm


Photometric data



MASTER LEDspot PAR 50W E27 827 25D





MASTER LEDspot PAR 50W E27 827 25D



MASTER LEDspot PAR 50W E27 827 25D

MASTER LEDspot PAR

Lifetime



MASTER LEDspot PAR 50W E27 827 25D

MASTER LEDspot PAR 50W E27 827 25D

