



LED PAR38

12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	12-90W

Light Technical	
Color Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	40 °
Initial lumen (Nom)	900 lm
Luminous Flux (Rated) (Nom)	900 lm
Luminous Intensity (Nom)	1900 cd
Color Designation	Cool White (CW)
Rated Beam Angle	40 °
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	12 W
Lamp Current (Nom)	112 mA

Wattage Equivalent	90 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	66 °C


Controls and Dimming	
Dimmable	Yes

Approval and Application	
Suitable For Accent Lighting	Yes

Product Data	
Order product name	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529680
Order code	529685
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001320204
Net Weight (Piece)	0.385 kg

LED PAR38


Dimensional drawing




Classic PAR38 120V 11-90W 900lm 40D 4000

Product	D	C
12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm


Photometric data



12-90W E26 PAR38 40D 840 4000K



12-90W E26 PAR38 40D 840 4000K



12-90W E26 PAR38

LED PAR38

Lifetime



14-120W E26 PAR38



14-120W E26 PAR38

