



Classic filament LEDbulbs

CLA LEDBulb D 5-40W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	5.5-40W

Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	470 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	85.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5.5 W
Lamp current (nom.)	38 mA

Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	50 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear

Approval and Application	
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	6 kWh


Classic filament LEDbulbs

Product Data

Full product code	871869670942900
Order product name	CLA LEDBulb D 5-40W A60 B22 827 CL
EAN/UPC – product	8718696709429
Order code	929001331102
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001331102
Net weight (piece)	0.030 kg


Dimensional drawing




Bulb A60 230V4.5-40W 470lm 2700K D Clear

Product	D	C
CLA LEDBulb D 5-40W A60 B22 827 CL	60 mm	102 mm


Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K



LEDbulb 40W B22 827 CL A60 D




LEDbulb 40W E27 827 CL A60 D

Classic filament LEDbulbs

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

