



# MASTER LEDspot ExpertColor LV

## MASTER LED ExpertColor 6.5-35W MR16 930 10D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV lamps.

### Product data

General Information	
Cap base	GU5.3 [GU5.3]
Nominal lifetime	40,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	930 [CCT of 3000K]
Beam angle (nom.)	10 degree(s)
Luminous Flux	430 lm
Luminous intensity (nom.)	5,000 cd
Colour designation	White (WH)
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	66.15 lm/W
Colour consistency	<3
Colour rendering index (CRI)	97
LLMF at end of nominal lifetime (nom.)	70 %

Luminous flux in 90° cone (rated)	430 lm
Operating and Electrical	
Line Frequency	- Hz
Input frequency	- Hz
Power Consumption	6.5 W
Lamp current (nom.)	800 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	ac electronic 12 V
Temperature	
T-Case maximum (nom.)	90 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb shape	MR16 [2 inch/50 mm]

Approval and Application	
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	8 kWh
EyeComfort	Yes

Product Data	
Order product name	MAS LED ExpertColor 6.5-35W MR16 930 10D



Full product name	MASTER LED ExpertColor 6.5-35W MR16 930 10D
Full EOC	871869673873300
Order code	73873300
Material no. (12 NC)	929001341802
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696738733
Numerator – packs per outer box	10
EAN/UPC – Case	8718696738740

Dimensional drawing



Product	D	C
MAS LED ExpertColor 6.5-35W MR16 930 10D	51 mm	46 mm

Photometric data




Accent Lighting Spots - MAS LED ExpertColor 6.5-35W MR16 930 10D

Light Distribution Diagram - MAS LED ExpertColor 6.5-35W MR16 930 10D


MASTER LEDspot ExpertColor LV

Photometric data




Spectral Power Distribution Colour - MAS LED ExpertColor 6.5-35W MR16 930 10D

Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 6.5-35W MR16 930 10D



Lumen Maintenance Diagram - MAS LED ExpertColor 6.5-35W MR16 930 10D

