

Corepro InstantFit (UL Type-A) T8

14T8/COR/48-840/IF21/G/DIM 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data

General Information		Color Consistency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Color rendering index (CRI)	<6
Nominal lifetime	70,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	50,000	Operating and Electrical	
Lighting Technology	LED	Line Frequency	25000-105000 Hz
EU RoHS compliant	Yes	Input Frequency	25000-105000 Hz
Light Technical		Power Consumption	14 W
Color Code	840 [CCT of 4000K]	Lamp Current (Max)	260 mA
Beam Angle (Nom)	240 degree(s)	Lamp Current (Min)	100 mA
Luminous Flux	2,100 lm	Wattage Equivalent	32 W
Color Designation	Cool White (CW)	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	4000 K	Warm-up time to 60% light	0.5 s
Luminous Efficacy (rated) (Nom)	150.00 lm/W	Power Factor (Fraction)	0.9

Corepro InstantFit (UL Type-A) T8


Voltage (Nom)	120-277, 347 V
UL Type	UL Type A
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance

Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	14T8/COR/48-840/IF21/G/DIM 10/1
Full product name	14T8/COR/48-840/IF21/G/DIM 10/1
Order code	470112
Material Nr. (12NC)	929001343234
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677453251
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677470116


Dimensional drawing

Product	D1	D2	A1	A2	A3
14T8/COR/48-840/IF21/G/DIM 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Photometric data




Light Distribution Diagram - 14T8/COR/48-840/IF21/G/DIM 10/1




Spectral Power Distribution Colour - 14T8/COR/48-840/IF21/G/DIM 10/1

Photometric data




Cellulose Monomer Unit	Monomer Unit	Monomer Unit
------------------------	--------------	--------------

Lifetime



Tc (°C)	Lumen (%)
50	100
55	99.25
60	98.5
65	97.75
70	96.5

Lumen Maintenance Diagram - 14T8/COR/48-840/IF21/G/DIM 10/1




Tc (°C)	B10L70 Life time (Hours)	B50L70 Life time (Hours)
50	45,000	70,000
55	36,000	58,000
60	27,000	44,000
65	23,000	37,000
70	19,000	30,000

Life Expectancy Diagram - 14T8/COR/48-840/IF21/G/DIM 10/1

Corepro InstantFit (UL Type-A) T8

Lifetime



Lumen Maintenance Diagram - 14T8/COR/48-840/IF21/G/DIM 10/1

