



SceneSwitch LEDspot

LED SSW 50W GU10 WW 36D RF ND 1BC/6

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LEDspot, you can have different light settings from just one spot. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	GU10 [GU10]	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.5
Switching Cycle	50,000	Voltage (Nom)		220-240 V
Lighting Technology	LED	Temperature		
EU RoHS compliant	Yes	T-Case Maximum (Nom)		80 °C
Light Technical		Controls and Dimming		
Color Code	827/825/822 [CCT of 2700K/2500K/2200K]	Dimmable		No
Beam Angle (Nom)	36 degree(s)	Mechanical and Housing		
Luminous Flux	345 lm	Bulb Shape		PAR16 [PAR 2 inch/50mm]
Color Designation	Warm/Extra Warm/Very Warm	Approval and Application		
Luminous Efficacy (rated) (Nom)	69.00 lm/W	Energy Consumption kWh/1000 h		5 kWh
Color Consistency	<6	EyeComfort		Yes
Color rendering index (CRI)	80	Product Data		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name		LED SSW 50W GU10 WW 36D RF ND 1BC/6
Operating and Electrical		Full product name		LED SSW 50W GU10 WW 36D RF ND 1BC/6
Line Frequency	50 to 60 Hz	Full product code		871869671093700
Input Frequency	50 to 60 Hz			
Power Consumption	1.5 3.5 5 W			
Lamp Current (Nom)	43 mA			

SceneSwitch LEDspot

Order code	929001346001
Material Nr. (12NC)	929001346001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696710937



Numerator - Packs per outer box	6
EAN/UPC - Case	8718696710944

Dimensional drawing




Product	D	C
LED SSW 50W GU10 WW 36D RF ND 1BC/6	50 mm	54 mm

Photometric data




Accent Lighting Spots - LED SSW 50W GU10 WW 36D RF ND 1BC/6

Light Distribution Diagram - LED SSW 50W GU10 WW 36D RF ND 1BC/6




Spectral Power Distribution Colour - LED SSW 50W GU10 WW 36D RF ND 1BC/6

Lifetime



Life Expectancy Diagram - LED SSW 50W GU10 WW 36D RF ND 1BC/6



Lumen Maintenance Diagram - LED SSW 50W GU10 WW 36D RF ND 1BC/6

