



# MASTER LEDspot ExpertColor MV



## MASTER LED ExpertColor 3.9–35W GU10 940 25D

MASTER LEDspot ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. They offer superior lighting that has a customized spectrum, high CRI, and deep dimming feature. What's more the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, with MASTER LEDspot ExpertColor you can take advantage of the full ExpertColor family, which also includes LEDspot MR16, LEDspot AR111 and LEDspot PAR lamps. MASTER LEDspot ExpertColor delivers huge energy savings and minimizes maintenance costs without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within a short time period.


### Product data

General Information			
Cap-Base	GU10	Correlated Color Temperature (Nom)	4000 K
Nominal lifetime	40,000 hour(s)	Luminous Efficacy (rated) (Nom)	76.00 lm/W
Switching Cycle	50,000	Color Consistency	<3
Lighting Technology	LED	Color rendering index (CRI)	97
Flux measurement reference	Narrow Cone	LLMF At End Of Nominal Lifetime (Nom)	70 %
CE mark	Yes	Luminous Flux in 90° Cone (Rated)	300 lm
EU RoHS compliant	Yes	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Light Technical		Stroboscopic effect visibility measure (SVM)	0.4
Color Code	940 [CCT of 4000K]	Photobiological safety according to EN 62471	RG1
Beam Angle (Nom)	25 degree(s)	Operating and Electrical	
Luminous Flux	300 lm	Line Frequency	50 to 60 Hz
Luminous Intensity (Nom)	800 cd	Input Frequency	50 to 60 Hz
Color Designation	Cool White (CW)	Power Consumption	3.9 W


# MASTER LEDspot ExpertColor MV

Lamp Current (Nom)	22 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V
<b>Temperature</b>	
T-Case Maximum (Nom)	80 °C
<b>Controls and Dimming</b>	
Dimmable	Only with specific dimmers
<b>Mechanical and Housing</b>	
Bulb Shape	PAR16
<b>Approval and Application</b>	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

## Dimensional drawing




## Photometric data



EPREL Registration Number	391829
EyeComfort	Yes
<b>Application Conditions</b>	
can it be used in closed luminaires	No
<b>Product Data</b>	
Order product name	MAS LED ExpertColor 3.9-35W GU10 940 25D
Full product name	MASTER LED ExpertColor 3.9-35W GU10 940 25D
Full product code	871869670753100
Order code	70753100
Material Nr. (12NC)	929001346602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707531
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707548

Product	D	C
MAS LED ExpertColor 3.9-35W GU10 940 25D	50 mm	54 mm




Accent Lighting Spots - MAS LED ExpertColor 3.9-35W GU10 940 25D

Spectral Power Distribution Colour - MAS LED ExpertColor 3.9-35W GU10 940 25D

# MASTER LEDspot ExpertColor MV

## Photometric data




Light Distribution Diagram - MAS LED ExpertColor 3.9-35W GU10 940 25D

## Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 3.9-35W GU10 940 25D



Lumen Maintenance Diagram - MAS LED ExpertColor 3.9-35W GU10 940 25D

