



MASTER LEDspot ExpertColor MV

MAS LED ExpertColor 5.5-50W GU10 927 24D

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look.

Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	40,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927
Beam Angle (Nom)	24 degree(s)
Luminous Flux	385 lm
Luminous Intensity (Nom)	1,000 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<3
Color rendering index (CRI)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	355 lm

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	30 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 ℃
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR16 [PAR 2 inch/50mm]


Datasheet, 2023, April 14 data subject to change

MASTER LEDspot ExpertColor MV

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	6 kWh
Product Data	
Order product name	MAS LED ExpertColor 5.5-50W GU10 927 24D
Full product name	MAS LED ExpertColor 5.5-50W GU10 927 24D
Full product code	871869675586000
Order code	929001347008


Material Nr. (12NC)	929001347008
Local order code	MEC385L24D927GU
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696755860
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696755877

Dimensional drawing




Product	D	С
MAS LED ExpertColor 5.5-50W GU10 927 24D	50 mm	54 mm

Photometric data



Circulat Processics 45 Philips Lighting BV. Pages 171


Accent Lighting Spots - MAS LED ExpertColor 5.5-50W GU10 927 24D



Spectral Power Distribution Colour - MAS LED ExpertColor 5.5-50W GU10 927 24D


MASTER LEDspot ExpertColor MV


Photometric data



Light Distribution Diagram - MAS LED ExpertColor 5.5-50W GU10 927 24D

Lifetime





Life Expectancy Diagram - MAS LED ExpertColor 5.5-50W GU10 927 24D

Lumen Maintenance Diagram - MAS LED ExpertColor 5.5-50W GU10 927 24D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.