



# MASTER VALUE LEDspot MV

## MASTER LED spot VLE D 3.7-35W GU10 930 60D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information		Luminous Intensity (Nom)	
Cap-Base	GU10 [GU10]		340 cd
Nominal lifetime	25,000 hour(s)	Color Designation	White (WH)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	3000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	81.08 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	270 lm
Light Technical		Operating and Electrical	
Color Code	930 [CCT of 3000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	60 degree(s)		
Luminous Flux	270 lm		

# MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	3.7 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

## Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------


## Controls and Dimming

Dimmable	Yes
----------	-----


## Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------

## Dimensional drawing



## Photometric data



Accent Lighting Spots - MAS LED spot VLE D 3.7-35W GU10 930 60D


## Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EyeComfort	Yes

## Product Data

Order product name	MAS LED spot VLE D 3.7-35W GU10 930 60D
Full product name	MASTER LED spot VLE D 3.7-35W GU10 930 60D
Full product code	871869670781400
Order code	70781400
Material Nr. (12NC)	929001348602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707814
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707821


Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 60D	50 mm	54 mm



Spectral Power Distribution Colour - MAS LED spot VLE D 3.7-35W GU10 930 60D


# MASTER VALUE LEDspot MV

## Photometric data




Light Distribution Diagram - MAS LED spot VLE D 3.7-35W GU10 930 60D

## Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 3.7-35W GU10 930 60D



Lumen Maintenance Diagram - MAS LED spot VLE D 3.7-35W GU10 930 60D

