



MASTER LEDspot MV Value

Master LED 5-50W GU10 927 36D Dim

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimises maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere. For environments where the right atmosphere needs to be created (e.g. bars and restaurants), the “DimTone” feature could be useful. This is a LED feature that creates a warmer tone once light is dimmed down to lower intensities.

Product data

General Information		Operating and Electrical	
Cap base	GU10 [GU10]	Colour Temperature, horizontal (Nom)	2700 K
Nominal lifetime (nom.)	25000 h	Lamp Luminous Efficacy EM (Nom)	80.61 lm/W
Switching cycle	50000X	Colour consistency	<6
Technical type	5-50W	Colour Rendering Index,horiz (Nom)	90
		LLMF at end of nominal lifetime (nom.)	70 %
		Luminous Flux in 90° Cone (Rated)	355 lm
Light Technical			
Colour Code	927	Input frequency	50 to 60 Hz
Technical Beam Angle (Nom)	36 °	Power (Rated) (Nom)	5 W
Lamp Luminous Flux 25°C EL (Nom)	395 lm	Lamp current (nom.)	27 mA
Luminous intensity (nom.)	650 cd	Wattage equivalent	50 W
Colour Designation	Warm white (WW)		

MASTER LEDspot MV Value

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case maximum (nom.)	80 °C
-----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes


Energy Consumption kWh/1000 h	5 kWh
-------------------------------	-------

Product Data

Full product code	871869670731900
Order product name	Master LED 5-50W GU10 927 36D Dim
EAN/UPC – product	8718696707319
Order code	929001348808
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001348808
Net weight (piece)	0.038 kg

Warnings and Safety


Dimensional drawing




GU10 230V5W-50W 345lm 36D 2700K GU10 Dim

Product	D	C
Master LED 5-50W GU10 927 36D Dim	50 mm	54 mm

Photometric data




MASTER LEDspotMV 50W GU10 927 36D 355lm



MASTER LEDspotMV 35W GU10 927 36D 260lm



MASTER LEDspot MV Value

Photometric data



MASTER LEDspotMV 50W GU10 36D 355lm

Lifetime



MASTER LEDspotMV GU10 922-927 36D

MASTER LEDspotMV GU10 922-927 36D

