



MASTER VALUE LEDspot MV



MASTER LED spot VLE D 4.9-50W GU10 930 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	365 lm
Luminous Intensity (Nom)	650 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color Consistency	<6

MASTER VALUE LEDspot MV

Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	365 lm
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG1

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.9 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Shape	PAR16
------------	-------

Approval and Application

Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	391888
EyeComfort	Yes


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	MAS LED spot VLE D 4.9-50W GU10 930 36D
Full product name	MASTER LED spot VLE D 4.9-50W GU10 930 36D
Full product code	871869670787600
Order code	70787600
Material Nr. (12NC)	929001348902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707876
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707883


Dimensional drawing




Product	D	C
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm

MASTER VALUE LEDspot MV


Photometric data



Accent Lighting Spots - MAS LED spot VLE D 4.9-50W GU10 930 36D




Spectral Power Distribution Colour - MAS LED spot VLE D 4.9-50W GU10 930 36D




Light Distribution Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D



Lumen Maintenance Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D

MASTER VALUE LEDspot MV

