# **PHILIPS** Lighting



# MASTER VALUE LEDspot MV

# Master LED 4.9-50W GU10 930 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiences for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings that normal LED spots.

#### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

#### **Product data**

General Information		Luminous Intensity (Nom)	650 cd
Cap-Base	GU10	Color Designation	White (WH)
Nominal lifetime	25,000 hour(s)	Correlated Color Temperature (Nom)	3000 K
Switching Cycle	50,000	Luminous Efficacy (rated) (Nom)	81.00 lm/W
Lighting Technology	LED	Color Consistency	<6
EU RoHS compliant	Yes	Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Luminous Flux in 90° Cone (Rated)	365 lm
Color Code	930 [CCT of 3000K]		
Beam Angle (Nom)	36 degree(s)	Operating and Electrical	
Luminous Flux	405 lm	Line Frequency	50 to 60 Hz

### MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR16

Approval and Application		
Suitable For Accent Lighting	Yes	
Energy Consumption kWh/1000 h	5 kWh	
Product Data		
Order product name	Master LED 4.9-50W GU10 930 36D Dim	
Full product name	Master LED 4.9-50W GU10 930 36D Dim	
Full product code	871869675592100	
Order code	929001348908	
Material Nr. (12NC)	929001348908	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718696755921	
Numerator - Packs per outer box	10	

8718696755938


D

с

EAN/UPC - Case

Product

#### **Dimensional drawing**




Master LED 4.9-50W GU10 930 36D Dim	50 mm	54 mm

# 100 80 40 20 0 200 300 400 500 600 700 800 $\lambda[nm]$

Spectral Power Distribution Colour - Master LED 4.9-50W GU10 930 36D Dim


## Photometric data



Accent Lighting Spots - Master LED 4.9-50W GU10 930 36D Dim


#### MASTER VALUE LEDspot MV


#### Photometric data



Light Distribution Diagram - Master LED 4.9-50W GU10 930 36D Dim

#### Lifetime





Life Expectancy Diagram - Master LED 4.9-50W GU10 930 36D Dim

Lumen Maintenance Diagram - Master LED 4.9-50W GU10 930 36D Dim



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 16 - data subject to change