



# MASTER LEDspot MV Value

## Master LED 5-50W GU10 940 36D Dim

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimises maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere. For environments where the right atmosphere needs to be created (e.g. bars and restaurants), the “DimTone” feature could be useful. This is a LED feature that creates a warmer tone once light is dimmed down to lower intensities.

### Product data

General Information	
Cap base	GU10 [ GU10]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	5-50W
Light Technical	
Colour Code	940 [ CCT of 4,000 K]
Technical Beam Angle (Nom)	36 °
Lamp Luminous Flux 25°C EL (Nom)	420 lm
Lamp Luminous Flux (Nom)	420 lm
Luminous intensity (nom.)	700 cd

Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Lamp Luminous Efficacy EM (Nom)	84.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	380 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Lamp current (nom.)	27 mA

## MASTER LEDspot MV Value

Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V

### Temperature

T-Case maximum (nom.)	80 °C
-----------------------	-------

### Controls and Dimming

Dimmable	Yes
----------	-----

### Approval and Application

Energy efficiency label (EEL)	A+
-------------------------------	----


Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	5 kWh

### Product Data

Full product code	871869675594500
Order product name	Master LED 5-50W GU10 940 36D Dim
EAN/UPC – product	8718696755945
Order code	929001349008
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001349008
Net weight (piece)	0.038 kg

## Warnings and Safety


### Dimensional drawing



GU10 230V5W-50W 365lm 36D 4000K GU10 Dim


Product	D	C
Master LED 5-50W GU10 940 36D Dim	50 mm	54 mm

### Photometric data



General Information 41 Photo Lighting 41 Page 107


MASTER LEDspotMV 50W GU10 940 36D 380lm



MASTER LEDspotMV 35W GU10 940 36D 285lm

# MASTER LEDspot MV Value

## Photometric data



MASTER LEDspotMV 50W GU10 36D 355lm

## Lifetime



MASTER LEDspotMV GU10 922-927 36D



MASTER LEDspotMV GU10 922-927 36D

