



# MASTER VALUE LEDspot MV

## MASTER LED spot VLE D 7-80W GU10 830 36D

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information		Luminous intensity (nom.)	
Cap base	GU10 [GU10]		1,200 cd
Nominal lifetime	25,000 h	Colour designation	White (WH)
Switching Cycle	50,000	Correlated Colour Temperature	3000 K
Lighting Technology	LED	Luminous efficacy (rated) (nom.)	84.29 lm/W
EU RoHS compliant	Yes	Colour consistency	<6
		Colour rendering index (CRI)	80
		LLMF at end of nominal lifetime (nom.)	70 %
		Luminous flux in 90° cone (rated)	590 lm
Light Technical		Operating and Electrical	
Colour Code	830 [CCT of 3000K]	Line Frequency	50 to 60 Hz
Beam angle (nom.)	36 degree(s)		
Luminous Flux	590 lm		

# MASTER VALUE LEDspot MV

Input frequency	50 to 60 Hz
Power Consumption	7 W
Lamp current (nom.)	35 mA
Wattage equivalent	80 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V

## Temperature

T-Case maximum (nom.)	85 °C
-----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb shape	PAR16 [PAR 2 inch/50 mm]
------------	--------------------------


## Approval and Application

Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	7 kWh
EyeComfort	Yes

## Product Data



Order product name	MAS LED spot VLE D 7-80W GU10 830 36D
Full product name	MASTER LED spot VLE D 7-80W GU10 830 36D
Full EOC	871869670797500
Order code	70797500
Material no. (12 NC)	929001349402
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696707975
Numerator – packs per outer box	10
EAN/UPC - Case	8718696707982

## Dimensional drawing



Product	D	C
MAS LED spot VLE D 7-80W GU10 830 36D	50 mm	54 mm

## Photometric data




Accent Lighting Spots - MAS LED spot VLE D 7-80W GU10 830 36D

Light Distribution Diagram - MAS LED spot VLE D 7-80W GU10 830 36D


# MASTER VALUE LEDspot MV

## Photometric data




Spectral Power Distribution Colour - MAS LED spot VLE D 7-80W GU10 830 36D

## Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 7-80W GU10 830 36D



Lumen Maintenance Diagram - MAS LED spot VLE D 7-80W GU10 830 36D

