PHILIPS Lighting



MASTER VALUE LEDspot MV

MASTER LED spot VLE DT 3.7-35W GU10 927 36D

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data


General Information		Luminous intensity (nom.)	500 cd
Cap base	GU10 [GU10]	Colour designation	Warm White (WW)
Nominal lifetime	25,000 h	Correlated Colour Temperature	2700 K
Switching Cycle	50,000	Luminous efficacy (rated) (nom.)	78.38 lm/W
Lighting Technology	LED	Colour consistency	<6
EU RoHS compliant	Yes	Colour rendering index (CRI)	90
		LLMF at end of nominal lifetime (nom.) 70 %	
Light Technical		Luminous flux in 90° cone (rated)	260 lm
Colour Code	922-927 [CCT of 2200K-2700K]		
Beam angle (nom.)	36 degree(s)	Operating and Electrical	
Luminous Flux	260 lm	Line Frequency	50 to 60 Hz

MASTER VALUE LEDspot MV

Input frequency	50 to 60 Hz
Power Consumption	3.7 W
Lamp current (nom.)	20 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	PAR16 [PAR 2 inch/50 mm]


Approval and Application		
Suitable for accent lighting	Yes	
Energy consumption kWh/1,000 hours	4 kWh	
EyeComfort	Yes	
Product Data		
Order product name	MAS LED spot VLE DT 3.7-35W GU10 927 36D	
Full product name	MASTER LED spot VLE DT 3.7-35W GU10 927	
	36D	
Full EOC	871869670809500	
Order code	70809500	
Material no. (12 NC)	929001350002	
SAP numerator – quantity per pack	1	
EAN/UPC — Product/Case	8718696708095	
Numerator – packs per outer box	10	
EAN/UPC - Case	8718696708101	

Dimensional drawing




Product	D	с
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm

Photometric data








Light Distribution Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D


MASTER VALUE LEDspot MV

Photometric data




Accent Lighting Spots - MAS LED spot VLE DT 3.7-35W GU10 927 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D



Lumen Maintenance Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change