



# MASTER VALUE LEDspot MV



## MASTER LED spot VLE DT 4.9-50W GU10 927 36D

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime	25,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Colour Code	922-927 [CCT of 2200K-2700K]


Beam angle (nom.)	36 degree(s)
Luminous Flux	355 lm
Luminous intensity (nom.)	650 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	80.61 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	355 lm
Flickering value (PstLM)	1

MASTER VALUE LEDspot MV

Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4.9 W
Lamp current (nom.)	27 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb shape	PAR16 [PAR 2 inch/50 mm]

Approval and Application	
Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	5 kWh
EPREL registration number	400288
EyeComfort	Yes
Product Data	
Order product name	MAS LED spot VLE DT 4.9-50W GU10 927 36D
Full product name	MASTER LED spot VLE DT 4.9-50W GU10 927 36D
Full EOC	871869670811800
Order code	70811800
Material no. (12 NC)	929001350302
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696708118
Numerator – packs per outer box	10
EAN/UPC – Case	8718696708125


Dimensional drawing




Product	D	C
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm

MASTER VALUE LEDspot MV


Photometric data



Spectral Power Distribution Colour - MAS LED spot VLE DT 4.9-50W GU10 927 36D




Light Distribution Diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D




Technical drawing of the MAS LED spot VLE DT 4.9-50W GU10 927 36D

Accent Lighting Spots - MAS LED spot VLE DT 4.9-50W GU10 927 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D



Lumen Maintenance Diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D

## MASTER VALUE LEDspot MV

