



# MASTER Plastic LEDbulbs

## MAS LED bulb DT 5.5-40WE27 927-922 A60FR

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information		Light Technical	
Cap-Base	E27 [E27]	Color Code	922-927 [CCT of 2200K-2700K]
Nominal lifetime	25,000 hour(s)	Beam Angle (Nom)	200 degree(s)
Switching Cycle	100,000	Luminous Flux	470 lm
Lighting Technology	LED	Color Designation	Warm White (WW)
EU RoHS compliant	Yes	Luminous Efficacy (rated) (Nom)	85.00 lm/W
		Color Consistency	<6

MASTER Plastic LEDbulbs

Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	31 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.3 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

Bulb Shape	A60 [A 60mm]
------------	--------------


Approval and Application

Energy Consumption kWh/1000 h	6 kWh
-------------------------------	-------

Product Data

Order product name	MAS LED bulb DT 5.5-40WE27 927-922 A60FR
Full product name	MAS LED bulb DT 5.5-40WE27 927-922 A60FR
Full product code	871869670709800
Order code	929001351302
Material Nr. (12NC)	929001351302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707098
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707104


Dimensional drawing




Product	D	C
MAS LED bulb DT 5.5-40WE27 927-922 A60FR	60 mm	110 mm

MASTER Plastic LEDbulbs


Photometric data



General uniform lighting - MAS LED bulb DT 5.5-40WE27 927-922 A60FR




Spectral Power Distribution Colour - MAS LED bulb DT 5.5-40WE27 927-922 A60FR




Light Distribution Diagram - MAS LED bulb DT 5.5-40WE27 927-922 A60FR

Lifetime



Life Expectancy Diagram - MAS LED bulb DT 5.5-40WE27 927-922 A60FR



Lumen Maintenance Diagram - MAS LED bulb DT 5.5-40WE27 927-922 A60FR

## MASTER Plastic LEDbulbs

