



MASTER LEDspot PAR

Master LED PAR30L 32W 30D 857

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	32-50W
Light Technical	
Colour code	857 [CCT of 5,700 K]
Beam Angle (Nom)	30 °
Luminous flux (nom.)	3000 lm
Colour designation	Daylight
Correlated colour temperature (nom.)	5700 K
Luminous efficacy (rated) (nom.)	93.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	82
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	32 W
Lamp current (nom.)	160 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	79 °C
Controls and Dimming	
Dimmable	No

MASTER LEDspot PAR

Approval and Application


Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	32 kWh

Product Data

Full product code	871869673148200
Order product name	Master LED PAR30L 32W 30D 857

EAN/UPC – product	8718696731482
Order code	73148200
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001354908
Net weight (piece)	0.410 kg


Dimensional drawing




PAR30L 220-240V 32-70W 30D 5700K E27 ND

Product	D	C
Master LED PAR30L 32W 30D 857	95.5 mm	129 mm


Photometric data



LEDspot PAR30L E27 5700K 30D



LEDspot PAR30L E27 5700K 30D



LEDspot PAR30L E27 5700K 30D

MASTER LEDspot PAR

Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

