



MASTER LEDspot PAR

Master LED PAR30L 40W 30D 827

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

| General Information | |
|--------------------------------------|-----------------------|
| Cap base | E27 [E27] |
| Nominal lifetime (nom.) | 25000 h |
| Switching cycle | 50000X |
| Technical type | 40-70W |
| Light Technical | |
| Colour Code | 827 [CCT of 2,700 K] |
| Beam Angle (Nom) | 30 ° |
| Lamp Luminous Flux 25°C EL (Nom) | 4300 lm |
| Lamp Luminous Flux (Nom) | 4300 lm |
| Luminous intensity (nom.) | 13000 cd |
| Colour Designation | Warm white (WW) |
| Colour Temperature, horizontal (Nom) | 2700 K |
| Lamp Luminous Efficacy EM (Nom) | 107.00 lm/W |
| Colour consistency | <6 |
| Colour Rendering Index,horiz (Nom) | 82 |

| LLMF at end of nominal lifetime (nom.) | 70 % |
|--|-------------|
| Operating and Electrical | |
| Input frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 40 W |
| Lamp current (nom.) | 196 mA |
| Wattage equivalent | 70 W |
| Starting time (nom.) | 0.5 s |
| Warm-up time to 60% light (nom.) | 0.5 s |
| Power factor (nom.) | 0.9 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case maximum (nom.) | 90 °C |

MASTER LEDspot PAR

Controls and Dimming

| | |
|----------|----|
| Dimmable | No |
|----------|----|

Approval and Application


| | |
|-------------------------------|--------|
| Energy efficiency label (EEL) | A+ |
| Suitable for accent lighting | Yes |
| Energy Consumption kWh/1000 h | 40 kWh |

Product Data

| | |
|-------------------|-----------------|
| Full product code | 871869675939400 |
|-------------------|-----------------|

| | |
|---------------------------------|-------------------------------|
| Order product name | Master LED PAR30L 40W 30D 827 |
| EAN/UPC – product | 8718696759394 |
| Order code | 929001374708 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 6 |
| Material no. (12NC) | 929001374708 |
| Net weight (piece) | 0.410 kg |


Dimensional drawing




PAR30L 40-35W 4500lm 30D 2700K E27 ND

| Product | D | C |
|-------------------------------|---------|--------|
| Master LED PAR30L 40W 30D 827 | 95.5 mm | 129 mm |

Photometric data




LEDspot MAS 41W E27 PAR30L 827 30D ND



LEDspot MAS 41W E27 PAR30L 827 30D ND

MASTER LEDspot PAR


Photometric data




© 2020 Philips Lighting B.V. Philips Lighting B.V. Page 10

LEDspot MAS 41W E27 PAR30L 827 30D ND

Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

